



DECHLORINATION / DECHLORAMINATION

BACTERIOSTATIC

5 MICRON FILTRATION

What is Cerapure-AC?

Cerapure-AC is a proprietary blend* of metal alloy and activated carbon permanently attached to a highly textured, ceramic granular substrate.

Where is it used?

Cerapure-AC is ideal for applications where high levels of chemical oxidants are used for the removal of iron, manganese and hydrogen sulfide. Cerapure-AC will provide removal of oxidation levels simultaneously preventing oxidants from entering the filtrate.

The use of metal alloy prevents biological fouling of the media and ensures a longer active life than any other media.

Cerapure-AC provides significantly improved filtration performance as compared to GAC or Alloy mono-medias. Its small effective size and low uniformity coefficient ensures excellent particle removal and retention.

PRODUCT SPECIFICATIONS

| Parameter | Cerapure-AC** |
|-------------------------------------|--|
| Multiple Effective Sizes available: | 0.25 mm – 0.30 mm |
| Uniformity Coefficient | < 1.4 (1.25 typical) |
| Density | 89 lbs/ft³ (1.4 g/cm³) |
| Recommended Bed Depth | 24" (61 cm) |
| Recommended Service Flow Rate | 8.0 gpm/ft ² (20 m/hr) |
| Backwash Rate (See Curves) | 10-12 gpm/ft ² (25 m/hr) TYP. |
| Operational pH | 6.2 – 9.5 |



Cerapure-AC is ideal for applications such as:

- Oxidation Reduction (Cl2, H2O2, Ozone, Chloramines)
- Biologically active feed water
- Where bacterial growth may occur in an off-line filter
- > 90% removal of 5-micron particles

Cerapure-AC does not require "conditioning" at installation, just backwash it and put it into service. Various effective sizes and uniformity coefficients are available upon request.**

Performance**

- 10" deep bed
- 3 minute Empty Bed Contact Time:
 - >95% removal of chlorine
 - >90 % removal of chloramines



Cerapure-AC process media certified by IAPMO R&T against NSF/ANSI 61 for Materials Safety Requirements only.




^{*} Patent pending


^{**} Tests and stated results are by Wateropolis and have not been independently validated.

CERAPURE-AC



OPERATIONAL DATA





Backwash and pressure drop curves for different size material is available upon request.

Operational data for other filter media sizes is available upon request.

*Patent pending





ABOUT WATEROPOLIS Wateropolis Inc. is dedicated to identifying and developing new and innovative technologies for water and wastewater treatment. We look for simple, logical answers to complex questions.